



AUSFÜHRUNG FÜR SIMONS-VOSS AKTIV

Achtung! SimonsVoss Aktiv wird serienmäßig mit geschlossener Front geliefert.

DigiSafe Standard

Der GEMINY DigiSafe Standard baut auf einem komplett neuen Funktionskonzept auf. Durch den aufschraubbaren Ring ergibt sich für die Mitnahme des Knaufzylinders eine enorme Flexibilität und Montagefreundlichkeit. Ungenauigkeiten durch nicht exakt zentrische Montage oder Spannungen an Schloss oder Zylinder können so bestmöglich ausgeglichen werden. Durch die von uns neu entwickelte Kugellagerung läuft der Knauf des DigiSafes besonders rund und ohne Widerstand.

DigiSafe Standard

The GEMINY DigiSafe standard model is based on a completely new functional concept. The fixation ring ensures best force transmission, flexibility and an easy way to install the product on the door. Inaccuracies by not exact centric assembly or tensions of the lock or cylinder can optimally be cleared. The new ball bearing that has been developed by us guarantees the DigiSafes knob to rotate round and without resistance.

